

Product Information ISO Class 5 – 8 Cleanroom Class 100 – 100,000 EU Grade B/C/D

# Durx<sup>®</sup> 670A 55% Cellulose / 45% Polyester Nonwoven Cleanroom Wiper

Durx<sup>®</sup> 670A is a cellulose / polyester nonwoven wiper recommended for ISO Class 5 and above environments composed of a hydroentangled nonwoven blend of 55% for controlled environments and cellulose and 45% polyester. This combination of

properties provides Durx<sup>®</sup> 670A with the level of absorben- applications where both cleanliness and economy are of cy, abrasion resistance and chemical compatibility required the most importance. for controlled environments and



#### Other ISO Class 5 and above nonwoven wipers

- BlueSorb<sup>®</sup> 750
- Durx<sup>®</sup> 770
- MicroFirst<sup>®</sup>
- MicroFirst LP<sup>®</sup>
- ProjX<sup>®</sup> 700
- Pro-Wipe® 750
- Pro-Wipe® 880
- SunSorb<sup>®</sup> 450
- ValuClean® Plus

#### Key Attributes

- 55% cellulose / 45% polyester hydroentangled nonwoven blend
- No binders or other chemical additives

#### **Benefits**

- Excellent combination of the synthetic polyester strength and cleanliness with the absorbent characteristics of cellulose
- Smooth, highly absorbent and durable
- Low extractable levels and particle counts
- Chemically compatible with common cleaning and disinfecting solutions
- Autoclavable
- Economical

#### Applications

- Designed for use in ISO Class 5 and higher cleanroom environments
- General equipment wrap and wipe downs
- General purpose wiping applications
- Cleaning of lab equipment
- · General wiping in component prep, compounding and wash areas
- Applying and removing cleaning and disinfecting solutions

#### Environmental

- Complies with RoHS
- 55% cellulose fiber content is biodegradable

#### **Pre-Wetted Option**

The same wiper material can be provided in pre-wetted formats for reduced VOC emissions, increased convenience, increased productivity, improved solvent control and cleaning protocol repeatability and reduced costs.

#### **Sterile Validated Option**

For aseptic processing areas, the same wiper material can be provided in a gamma irradiated validated sterile to a 10<sup>-6</sup> sterility assurance level. Dry and pre-wetted versions available.

## www.berkshire.com.sg

Contact: Tel: 65.6252.4313 Fax: 65.6252.4312 Email: enquiries@berkshire.com.sg

America	Tel 1 413 528 2602	Fax 1 413 528 2614	info@berkshire.com
Europe	Tel 44 (0) 870 757 2877	Fax 44 (0) 870 757 2878	enquiries@berkshire.uk.com
SE Asia	Tel 65 6252 4313	Fax 65 6252 4312	enquiries@berkshire.com.sg
Japan	Tel 81 3 5827 2380	Fax 81 3 5827 2382	master@berkshire.co.jp



#### **Technical Data:**

Attribute		Units	Value	Test Method
Basis Weight		g/m <sup>2</sup>	68.0	TAPPI T-410
Caliper		μm	300	TAPPI T-411
Fibers	≥100µm	fibers/cm <sup>2</sup>	130	IEST-RP-CC004.3, Sec 6.1.3 / Sec 6.2.2
Particles	≥ <b>0.</b> 5µm	x10 <sup>3</sup> /cm <sup>2</sup>	6.3	IEST-RP-CC004.3, Sec 6.1.3 / Sec 6.2.1
Sorbency	Capacity	mL/m <sup>2</sup>	307	IEST-RP-CC004.3, Sec 8.1 modified / Sec 8.2 modified
	Efficiency	mL/g	4.5	
	Rate	seconds	2	
Non-Volatile Residue	DI Water	g/m <sup>2</sup>	0.040	IEST-RP-CC004.3, Sec 7.1.2
	IPA	g/m²	0.0068	
Ions	Na⁺	ppm	60	IEST-RP-CC004.3, Sec 7.2.2
	K+	ppm	10	
	Ca++	ppm	20	
	Mg <sup>++</sup>	ppm	4.0	
	CI	ppm	15	

Notes:

• Technical data represented in this table are typical values at the time of publication. These should not be used as product specifications.

• Due to differences in test methods applied and equipment utilized by different wiper manufacturers, valid product comparisons may only be obtained through side-by-side testing in the same test facility, under similar conditions

### **Order Information:**

Product	Number	Size	Shts/pk	Pks/cs	Style
Durx <sup>®</sup> 670A	DR670A.0404.10	4x4" (10x10cm)	1200	10	Stacked
Durx <sup>®</sup> 670A	DR670A.0606.15	6x6" (15x15cm)	300	15	Stacked
Durx <sup>®</sup> 670A	DR670A.0707.45	7x7" (18x18cm)	300	45	Stacked
Durx <sup>®</sup> 670A	DR670A.0909.10	9x9" (23x23cm)	300	10	Stacked
Durx <sup>®</sup> 670A	DR670A.0909.20	9x9" (23x23cm)	300	20	Stacked



## www.berkshire.com.sg

Contact: Tel: 65.6252.4313 / enquiries@berkshire.com.sg